

SYNC Profi single-lever mixer - Chrome

SYNC

33 865 895 Product version from 2/4/2019



- 200mm projection
- Flexible silicone hose with large operating range of up to 350 mm
- pivotable spout 360°
- Optional swivel limiter available with swivel limiter set 12 821 970 90
- This product can help a building meet the requirements of Green Building Rating Systems, e.g. LEED®, BREEAM®, DGNB
- air-enriched flow and spray flow
- height of mixer 451 mm
- height up to aerator 119 mm
- hole diameter 35 mm
- sprayface with anti-scaling system
- max. flow 9.5 l/min at 3 bar flow pressure
- lead-free

Intrinsic protection against back flow.

	Chrome	33 865 895-00
	Brushed Platinum	33 865 895-06
	Platinum	33 865 895-08
	Durabronze (23kt Gold)	33 865 895-09
	Dark Chrome	33 865 895-19
	Brushed Durabronze (23kt Gold)	33 865 895-28
	Matte Black	33 865 895-33
	Brushed Bronze	33 865 895-42
	Brushed Champagne (22kt Gold)	33 865 895-46
	Champagne (22kt Gold)	33 865 895-47
	Brushed Chrome	33 865 895-93
	Brushed Dark Platinum	33 865 895-99

Recommended miscellaneous

Swivel limitation set -

12 821 970 90



Recommended miscellaneous

Dispenser without rosette - Chrome

82 424 970-00




Recommended miscellaneous

Strainer waste with control handle - Chrome

10 712 970-00





Flow rate chart



Codes & Standards

DIN 4109

EN 1717

ISO 3822

Ü-Zeichen



SYNC Profi single-lever mixer - Chrome

SYNC

33 865 895 Product version from 2/4/2019

Certificates and sustainability

Belgaqua_21-027-2 LGA_29



Spare parts list

No.	Item Number	Name	Quantity used	Delivery time
10	09 20 89 020-00	handle	1.00	10
9	09 28 30 030-00	cover	1.00	10
12	90 31 20 087 00-00	plug	1.00	10
13	04 30 11 040 00 90	fixing set	1.00	2
2	09 31 11 040 90	pin	1.00	2
5	04 12 11 150 00 90	shower	1.00	2
14	04 30 04 101 00 90	hose	2.00	2
1	90 30 02 100 00-00	hose	1.00	10
8	09 14 10 190 90	seal	1.00	2
3	09 31 11 209 90	pin	1.00	2
4	90 17 20 045 00-00	holder	1.00	10
11	90 31 11 063 00 90	pin	1.00	2
7	90 15 05 064 05 90	cartridge	1.00	2
6	12 821 970 90	Swivel limitation set -	1.00	2