












META Wall-mounted single-lever basin mixer without pop-up waste - Brushed Platinum


META

36 805 661	Product version from 4/1/2024		
	<ul style="list-style-type: none"> 160mm projection fixed spout circular, air-enriched flow hole diameter 60 mm rosette Ø 78 mm max. spout flow rate 5.7 l/min with single-point mounting 		<div>Brushed Platinum</div> <div>36 805 661-06</div>
			<div>Chrome</div> <div>36 805 661-00</div>
			<div>Dark Chrome</div> <div>36 805 661-19</div>
			<div>Light Gold</div> <div>36 805 661-26</div>
			<div>Brushed Light Gold</div> <div>36 805 661-27</div>
			<div>Matte Black</div> <div>36 805 661-33</div>
			<div>Brushed Bronze</div> <div>36 805 661-42</div>
			<div>Brushed Champagne (22kt Gold)</div> <div>36 805 661-46</div>
			<div>Champagne (22kt Gold)</div> <div>36 805 661-47</div>
			<div>Brushed Chrome</div> <div>36 805 661-93</div>
			<div>Brushed Dark Platinum</div> <div>36 805 661-99</div>


Required miscellaneous

	<div> <div> <div>Concealed wall mounting -</div> <div> <ul style="list-style-type: none"> min. recess depth 80 mm max. recess depth 105 mm </div> </div> <div>35 050 970 90</div> </div>	
--	--	--

36 805 661 Product version from 4/1/2024



Flow rate chart



Codes & Standards

DIN 4109

ISO 3822

Ü-Zeichen




META Wall-mounted single-lever basin mixer without pop-up waste - Brushed Platinum

META

36 805 661 Product version from 4/1/2024

Certificates and sustainability

LGA_38



Spare parts list

No.	Item Number	Name	Quantity used	Delivery time
10	90 23 01 168 00-06	aerator	1.00	10
4	09 31 11 144 90	pin	1.00	2
2	90 24 01 046 01 90	connection	2.00	2
8	09 28 30 043-06	cover	1.00	10
11	90 30 30 229 00 90	screw	2.00	2
3	90 27 66 026 00-06	rosette	1.00	10
7	09 14 10 120 90	seal	1.00	2
9	90 20 66 024 00-06	handle	1.00	10
1	90 30 11 232 00 90	disc	1.00	2
6	09 24 04 266 90	nut	1.00	2
5	90 15 05 044 00 90	cartridge	1.00	2