









Towel warmer , 6-fold , projection left , without control element - Brushed Dark Platinum
SERIES SPECIFIC


83 306 980	Product version from 4/1/2025		
	<ul style="list-style-type: none"> gauge 120 mm width 600mm height 660 mm rosette 60 x 60 mm 63mm projection Degree of protection IP 44, CE marking Output per towel bar: 15 watts Rated voltage: 220 - 240 V AC Without control element Activation must be handled by the customer Note: Different conditioning. This appliance is a stationary electric space heater and, in order to comply with the mandatory ecodesign requirements of Commission Regulation (EU) 2024/1103, must be equipped with at least one control with control function TW(f2).	<div>  Brushed Dark Platinum 83 306 980-99 </div> <div>  Chrome 83 306 980-00 </div> <div>  Dark Chrome 83 306 980-19 </div> <div>  Matte Black 83 306 980-33 </div> <div>  Brushed Champagne (22kt Gold) 83 306 980-46 </div> <div>  Brushed Chrome 83 306 980-93 </div>	
	Without control element		
	Activation must be handled by the customer		
	Note: Different conditioning.		
	This appliance is a stationary electric space heater and, in order to comply with the mandatory ecodesign requirements of Commission Regulation (EU) 2024/1103, must be equipped with at least one control with control function TW(f2).		

Required miscellaneous

	Concealed wall installation box for 35 313 970 90 towel warmer , 6-fold , without control element - <ul style="list-style-type: none"> min. recess depth 70 mm max. recess depth 105 mm
---	--

Towel warmer , 6-fold , projection left , without control element - Brushed Dark Platinum SERIES SPECIFIC

83 306 980 Product version from 4/1/2025
mm [inches]




Towel warmer , 6-fold , projection left , without control element - Brushed Dark Platinum

SERIES SPECIFIC

83 306 980

Product version from 4/1/2025



Spare parts list

No.	Item Number	Name	Quantity used	Delivery time
1	90 17 98 561 00-99	holder	1.00	20
2	90 30 30 252 00 90	fixing set	1.00	30